

BJ745


スタッドボルト

標準 在庫品 R4HS

IMAO



BJ745-08~20 BJ745-24



タイプ	本体
BJ745-08~20	SCM435 焼入焼戻 四三酸化鉄皮膜 HRC33~39
BJ745-24	スチール 焼入焼戻 四三酸化鉄皮膜 HRC23~34

品番	M	L	L ₁	L ₂	D	質量 (g)
BJ745-08050	M 8×1.25	50	20	20	7.1	20
BJ745-08063		63	25	25		25
BJ745-08080		80	32	32		35
BJ745-08100		100				40
BJ745-08125		125				45
BJ745-08160	160	55				
BJ745-10050	M10×1.5	50	20	20	8.9	30
BJ745-10063		63	25	25		40
BJ745-10080		80	32	32		45
BJ745-10100		100	40	40		55
BJ745-10125		125				70
BJ745-10160		160				90
BJ745-10200	200	110				
BJ745-12050	M12×1.75	50	20	20	10.7	40
BJ745-12063		63	25	25		50
BJ745-12080		80	32	32		65
BJ745-12100		100	40	40		80
BJ745-12125		125				100
BJ745-12160		160				125
BJ745-12200	200	160				

品番	M	L	L ₁	L ₂	D	質量 (g)				
BJ745-16063	M16×2	63	25	25	14.5	90				
BJ745-16080		80	32	32		125				
BJ745-16100		100	40	40		145				
BJ745-16125		125				180				
BJ745-16160		160	50	50		230				
BJ745-16200		200				290				
BJ745-16250		250	63	63		360				
BJ745-16315		315				450				
BJ745-16400		400				570				
BJ745-16500		500				710				
BJ745-20080		M20×2.5				80	32	32	18.3	180
BJ745-20100			100	40		40	230			
BJ745-20125	125		280							
BJ745-20160	160		360							
BJ745-20200	200		50	50	460					
BJ745-20250	250				550					
BJ745-20315	315		63	63	690					
BJ745-20400	400				880					
BJ745-20500	500				1100					
BJ745-24100	M24×3				100	35	45	22		290
BJ745-24125					125		63			380
BJ745-24160			160	100	470					
BJ745-24200		200	125	580						
BJ745-24250		250	160	730						
BJ745-24315		315	200	920						
BJ745-24400		400	250	1160						
BJ745-24500		500	315	1460						

使用例・使用方法

